

# AUTOMATIC DISPENSER+QSEG CONNECTOR



QSEG MODULAR SEG DISPLAY  
PRODUCT CODE: QSEG-ADQC



Installed on QSEG 1.4 x 4.9ft

## PRODUCT DESCRIPTION

Automatic touch free hand sanitizer dispenser for QSEG Quick Wall Displays. The dispenser attaches to the top corners of either the left or right hand sides of your QSEG Quick Wall Display so it does not obstruct your graphic. Compatible with all QSEG Quick Wall Displays, but recommended for use on 4.9ft tall displays. Dispenser capacity is 1000ml and requires (qty 4) C batteries to operate (not included) or DC power 6V 1A plug (not included)

## RECOMMENDED DISPLAYS

FRAME SIZE	PRODUCT CODE
QSEG 1.4 x 4.9ft	QSEG-50x150
QSEG 3.3 x 4.9ft	QSEG-100x150
QSEG 4.9 x 4.9ft	QSEG-150x150

## CONSTRUCTION

Plastic dispenser with steel connector

## SHIPPING WEIGHTS & DIMENSIONS

Shipping Weight	3 lbs
Shipping Dimensions	12.5" W x 7.5" H x 5.25" D

## PRODUCT DETAILS

AVAILABILITY	PFC
POWER SOURCE	(Qty 4) C Batteries (not included)
DC PORT	6V 1A (plug not included)
DISPENSER VOLUME	1000ml
TOOLS REQUIRED	Wrench for 5mm nuts



Dispenser



Dispenser Open



Connecting Clip



Dispenser Installed

# AUTOMATIC DISPENSER+QSEG CONNECTOR

QSEG MODULAR SEG DISPLAY  
PRODUCT CODE: QSEG-ADQC



## PARTS LIST



(qty 1)  
Sanitizer Dispenser



(qty 1)  
Connecting Clip w/5mm Nuts




(qty 1)  
Key

# AUTOMATIC DISPENSER+QSEG CONNECTOR

QSEG MODULAR SEG DISPLAY  
PRODUCT CODE: QSEG-ADQC



## INSTRUCTIONS



Insert connector into the hole on the top corner of the frame



Pull open the sanitizer dispenser



Hook sanitizer dispenser onto the screws of the connector




Thread nuts onto connector screws to secure sanitizer dispenser onto the clip




Insert sanitizer tank into the housing



Insert (qty 4) C batteries and turn on side switch to power the dispenser on



Close dispenser cover and use provided key to lock



Wave hand under sensor to test dispenser